



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy



TECHSPEC® ACHROMATIC LENSES



SURFACE: IMA
DIA: 0.000 MM
SPOT DIAGRAM
47717
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 6.446
GD RADIUS : 13.107
SCALE BAR : 40
REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM
47717
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 297.3194 μm
DIFFRACTION LIMITED RANGE: 40.715 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT
47717
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM
47717
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



www.edmundoptics.com