



NOTES:

1. SUBSTRATE:
BOROFLOAT®
2. COATING SPECIFICATION:
S1: Protected Gold (700-10000nm)
R(AVG) >96% @ 700 - 2000nm
R(AVG) >96% @ 2000 - 10,000nm



3. FINE GROUND SURFACE

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2					
SHAPE	PLANO	PLANO					
SURFACE QUALITY	60-40	COMMERCIAL POLISH	THIRD ANGLE PROJECTION		TITLE	5 x 5mm Protected Gold, λ/4 Mirror	
CLEAR APERTURE	4.15 x 4.15	N/A	ALL DIMS IN	mm	DWG NO	48411	SHEET 1 OF 1
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					