





- NOTES:
 1. SUBSTRATE: UV FUSED SILICA
 2. ROHS: COMPLIANT

**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
SURFACE QUALITY	80-50
CENTER WAVELENGTH (nm)	253.7
FULL WIDTH HALF MAX (FWHM) (nm)	10±2
MIN TRANSMISSION (%)	12
CLEAR APERTURE	∅45.00
BEVEL	PROTECTIVE AS NEEDED



THIRD ANGLE PROJECTION		TITLE	253.7nm, 10nm FWHM, 50mm DIA. FIRST SURFACE UV BANDPASS FILTER
ALL DIMS IN	mm	DWG NO	14920
			SHEET 1 OF 1