



NOTES:

1. SUBSTRATE
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 10 ARCSEC
3. COATING (APPLY ACROSS CLEAR APERTURE)
 PHYSICAL DURABILITY: MIL-C-48497A
 ENVIRONMENTAL DURABILITY: MIL-STD-810F
 Tavg ≥93% @ 641.0 - 1427.4nm
4. FINE GROUND SURFACE
5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY
 ACROSS CLEAR APERTURE
6. TRANSMITTED WAVEFRONT DISTORTION RMS @ $\lambda/4$ @ 633nm
7. RoHS COMPLIANT

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
REJECTION WAVELENGTH	513 - 632.8	513 - 632.8
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	$\varnothing 40$	$\varnothing 40$
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN mm

EO® Edmund Optics®

TITLE: $\varnothing 50\text{mm}$, 639.1nm, RAMAN EDGE FILTER

DWG NO: 86260

SHEET 1 OF 1