




1. SUBSTRATE: Fused Silica (Corning 7980)
2. Coating: UNCOATED
3. Group Velocity Dispersion (fs²/mm): 36 @ 800nm
4. ROHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	
TYPE	DISPERSION PRISM
ANGLE TOL. (arcmin)	±3
CLEAR APERTURE	>80%
GROUP VELOCITY DISPERSION (fs ² /mm)	36
SURFACE QUALITY	20-10
SURFACE FLATNESS	λ/10
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm



TITLE

25.4 x 25.4mm, FUSED SILICA, ULTRAFast
PRISM

DWG NO

89845

SHEET
1 OF 1