



NOTES:

1. SUBSTRATE:
Alumoscilate Glass Embedded with Silver Ions
2. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: BBAR (450-700nm)
R(AVG) < 0.7%, 0 - 30°
3. EFL: 0.45
4. f/# : 0.9
5. NUMERICAL APERTURE: 0.54
6. DESIGN WAVELENGTH: 670nm
7. WORKING DISTANCE: 0mm ±0.02
8. ROHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION		TITLE	0.5mm Dia, 670nm DWL, 0.0mm WD, VIS Coated, GRIN Lens	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	64533	SHEET 1 OF 1
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	Ø0.45	Ø0.45					