



FOCAL LENGTH (EFL): 35 ± 0,35
 BACK FOCAL LENGTH (BFL): 31,58

- 1 AR COATING: UV-VIS
 R(AVG) ≤ 1,5% FROM 250-700nm @ 0° AOI
 R(ABS) ≤ 1,0% FROM 350-450nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	16,05±0,016 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	19		Øe	19
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 20mm Dia, x 35mm FL UV-VIS Coated, UV Plano-Convex Lens

DWG NO 49972

SHEET SIZE A4 SHEET 1 OF 1