




NOTES:

1. COATING:
S1: SPECTRAL BLACK™
THICKNESS: 3 - 7 (µm)
2. ABSORBANCE: 99.5 - 99.7 (0 - 10° AOI) %
3. ABRASION RESISTANCE: MODERATE
4. HUMIDITY RESISTANCE: MIL-C-48497A
5. OPERATING TEMPERATURE (°C): -196 TO +350
6. WAVELENGTH RANGE (µm): 0.3 - 14




DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	20 x 20cm Sheet of Spectral Black Foil, No Adhesive	
ALL DIMS IN	mm	DWG NO	20048	SHEET 1 OF 1